



Part Number : 1300980146

Series Number : 130098
Product Category : Cable Grips

Product Description : MAX-LOC Strain Relief
Cord-Sealing Grip, 1" NPT, Straight Male with
O-Ring, Cable Diameter 15.88-19.05mm (.625-
.750")
Status : Active
Engineering Number : 5552W

Documents & Resources

Drawings
Drawing 1300980146_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
--------	--------

Category	Cable Grips
Series	130098
Description	MAX-LOC Strain Relief Cord-Sealing Grip, 1" NPT, Straight Male with O-Ring, Cable Diameter 15.88-19.05mm (.625-.750")
NEMA Rating	NEMA 6P
Product Family	Strain-Relief Cord Grips
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678855522

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	15.88-19.05mm (.625-.750")
Color - Grommet	N/A
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Number of Holes	1
O-Ring	Yes
Thread Size	1" NPT

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 1" NPT	/content/molex/molex-dot-com/us/en/products/product-page.html/1300990145.html

This document was generated on Apr 12, 2024