

Part Number : 2171590520

Series Number : 217159

Product Category : Power and Signal Cable Assemblies

Product Description : Mini-Fit Jr.-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Single Row, 2.0m Length, 5 Circuits, Black

Status : Active

Documents & Resources

Drawings

Drawing 2171590520_sd.pdf

Specifications

Product Specification 4000358161-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	217159
Description	Mini-Fit Jr.-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Single Row, 2.0m Length, 5 Circuits, Black
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Single Ended Connector
Connector to Connector	Mini-Fit Jr.-to-Pigtail
Product Family	Mini-Fit Family Power Connectors
Product Name	Mini-Fit Jr.
Type	Overmolded Assembly
UPC	193264926374

Electrical

Current - Maximum per Contact	6.0A
-------------------------------	------

Physical

Cable Length	2.0m
Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Black
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	239.556/g
Number of Rows	1
Overmolded	Yes
Packaging Type	Bag
Pitch - Mating Interface	4.20mm

Plating min - Mating	0.889µm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 2464
Wire Insulation Diameter	1.80-3.10mm
Wire Size (AWG)	16

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini-Fit Jr. Plug Housing, Single Row, 2 Circuits, UL 94V-0, with Panel Mounting Ears, Natural	<u>469990657</u>
Mini-Fit Jr. Plug Housing, Single Row, 2 Circuits, UL 94V-0, without Panel Mounting Ears, Natural	<u>469990658</u>

This document was generated on Apr 15, 2024