

Part Number : 2178411125

Series Number : 217841

Product Category : Power and Signal Cable Assemblies

Product Description : Pre-Crimped Lead Mizu P25 Female-to-Pigtail, Tin (Sn) Plating, 450.00mm Length, 20 AWG, Black

Status : Active

Documents & Resources

Drawings

Drawing 2178411125_sd.pdf

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS |  |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2023)3788-DC (14 Jun 2023) |
| EU RoHS | Compliant per EU 2015/863 |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

| | |
|------------------------|---|
| Status | Active |
| Category | Power and Signal Cable Assemblies |
| Series | 217841 |
| Description | Pre-Crimped Lead Mizu-P25 Female-to-Pigtail, Tin (Sn) Plating, 450.00mm Length, 20 AWG, Black |
| Application | Signal, Wire-to-Wire |
| Assembly Configuration | Pre-crimped Lead Only |
| Connector to Connector | Mizu-P25 Terminal-to-Pigtail |
| Keyword | Pre-Crimped Leads |
| Product Family | Off-the-Shelf Pre-Crimped Leads |
| Product Name | Mizu-P25 |
| UPC | 195842149908 |

Electrical

| | |
|-------------------|------|
| Voltage - Maximum | 125V |
|-------------------|------|

Physical

| | |
|--------------------------------|----------------------|
| Cable Length | 450.00mm |
| Circuits (Loaded) | 1 |
| Circuits (maximum) | 1 |
| Color - Resin | Black |
| Gender | Female-Pigtail |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Net Weight | 3.020/g |
| Packaging Type | Bag |
| Single Ended | Yes |
| Termination Interface Style | Crimp or Compression |
| Wire/Cable Type | UL 10002 |
| Wire Insulation Diameter | 1.40-1.90mm |
| Wire Size (AWG) | 20 |

Use with Part(s)

| Description | Part Number |
|--|--------------|
| Mizu-P25 Waterproof Receptacle Housings | <u>52213</u> |

This document was generated on Jul 19, 2024