

Part Number : 1300000088

Series Number : 130000

Product Category : Circular Industrial Cordsets

Product Description : Quick-Change Single-Ended Cordset, 4 Poles, Female (Straight) to Pigtail, 12 AWG, Yellow CPE Cable, 1.83m (6.0') Length

Status : Active

Engineering Number : 32678

Documents & Resources

Drawings

Drawing 1300000088_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130000
Description	Quick-Change Single-Ended Cordset, 4 Poles, Female (Straight) to Pigtail, 12 AWG, Yellow CPE Cable, 1.83m (6.0') Length
IP Rating	IP67
Product Family	Brad Quick-Change Connectors
Product Name	Quick-Change
Region	America
Type	Single Ended
UPC	78678832678

Agency

CSA	LR6837
UL	E46237

Electrical

Current - Maximum per Contact	20.0A
Voltage - Maximum	600V

Physical

Cable Diameter	18.03mm (.710")
Cable Length	1.83m (6.0')
Color - Cable Jacket	Yellow
Connector End A	Quick-Change
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	CPE
Material - Connector Body	TPE
Material - Contact	Copper Alloy

Material - Coupling Nut	Nylon
Material - Plating Mating	N/A
Net Weight	736.633/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	SOW
Wire Size (AWG)	12

This document was generated on Apr 15, 2024