



产品编号：2147631101

系列号：214763

Product Category：Power and Signal Cable Assemblies

Product Description：Pre-Crimped Lead Micro-Fit 3.0 Male-to-Pigtail, Tin (Sn) Plating, 75.00mm Length, 22 AWG, Black
状态：Active

文件和资源

图纸
[图纸 2147631101_sd.pdf](#)

产物环境合规

合规

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

多部分产品合规性声明

- Eu RoHS
- REACH SVHC
- Low-Halogen
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

欧盟 RoHS 合格证书

产品详情

常规

状态	活动
类别	Power and Signal Cable Assemblies
系列	214763
说明	Pre-Crimped Lead Micro-Fit 3.0 Male-to-Pigtail, Tin (Sn) Plating, 75.00mm Length, 22 AWG, Black
应用	Power, Wire-to-Wire
组件配置	Pre-crimped Lead Only
连接器到连接器	Micro-Fit 3.0 Term-to-Pigtail
关键字	Pre-Crimped Leads
产品系列	Off-the-Shelf Pre-Crimped Leads
产品名称	Micro-Fit 3.0
UPC	193264574926

电气

每触点最大电流	8.5A
---------	------

物理

电缆长度	75.00mm
回路数（已载入）	1
电路数（最多）	1
颜色-树脂	黑色
性别	Male-Pigtail
材料 - 金属	Phosphor Bronze
材料 - 接合部位电镀	Tin
材料 - 终端电镀	Tin
净重	0.409/g
包装形式	Bag
最薄镀层 - 接合部位	1.016µm
最薄镀层 - 端接	1.016µm
单端的	是
终端界面类型	Crimp or Compression
导线/电缆型号	UL 10002
导线绝缘直径	1.85mm max.
线径规格（AWG）	22

可连接使用部件

描述	产品编号
Micro-Fit 3.0 Dual Row Plug Housings	<u>43020</u>
Micro-Fit 3.0 Single Row Plug Housings	<u>43640</u>
Micro-Fit BMI Dual Row Plug Housings	<u>44300</u>
Micro-Fit BMI Single Row Plug Housings	<u>46625</u>