








REV.	ECN NO OR DESCRIPTION	DRAW	DATE



CIRCUIT DIAGRAM



PCB.WELDING DRAWING

主要技术参数、性能
The Main Thchnology Performance

额定电流、电压 Rate voltage,current	50mA DC12V
接触电阻 Contact resistance	≤ 100mΩ
按力 Operating force	± 50gf
行程 Travel	0.35±0.15mm
绝缘电阻 Insulated resistance	≥ 100MΩ
介电强度 Dielectric strength	≥ 250VAC/1min

Part No	H(高度)	Part No	H(高度)
SMG-12T-H043A1	4.30	SMG-12T-H075A1	7.50
SMG-12T-H045A1	4.50	SMG-12T-H080A1	8.00
SMG-12T-H050A1	5.00	SMG-12T-H085A1	8.50
SMG-12T-H055A1	5.50	SMG-12T-H090A1	9.00
SMG-12T-H060A1	6.00	SMG-12T-H095A1	9.50
SMG-12T-H065A1	6.50	SMG-12T-H100A1	10.0
SMG-12T-H070A1	7.00		

G	按钮	PPA	1	黑色
F	盖板	PPA	1	黑色
E	防水层	硅胶	1	黑色
D	小按钮	PPA	1	黑色
C	弹片	磷铜/不锈钢	1	镀银
B	本体	PPA	1	黑色
A	卡件	黄铜	1	镀银
项目 ITEM	名称 DESCRIPTION	材质 MATERIAL	数量 QTY	表面处理/颜色 FINSH/COLOR

GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM	TITLE:	PART NO.	
		12*12*X贴片防水250GF	SMG-12T-HXXXXA1	
DISTANCE	ANGLE	 SM switch Co.,Ltd. 无锡斯茂科技有限公司 ISO 9001/ISO14001		
X. ±0.30	X.° ±2.0°			
.X ±0.20	.X° ±1.0°			
.XX ±0.15	.XX° ±0.5°			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	Matthew	THIRD ANGLE PRDJECTION		SHEET NO 1 OF 1
	Benjamin			
	Michael			
	/			
	Alexander			
	Sophia			