

A	B	C	D	E
REV.	DESCRIPTION	ECN NO.	NAME	DATE

1

(B+0.4)±0.3
A±0.1

2

1.27±0.1
3.00±0.15

SPECIFICATIONS
Current Rating: 1.0 Amps
Withstanding Voltage:AC 500V
Insulation Resistance:1000MQ Min
Contact Resistance:20mΩ Max
Operation Temperature:-40°to+105°
Insrlator Material:Polyester(UL94V-0)
Contact Material:Phosphor bronze
Standard:PA6T
Contact Plating:Gold Flash
Max.Processing Temp:240°C for30~60seconds
(260°C for5seconds)

3

Pin 0.45*0.15

4

1.27±0.1
1.27
ø0.60
A

RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

2.40±0.2
4.30±0.15

P/N	PIN	DIM.A	DIM.B
B127UP-ZS1P	1	0.00	1.27
B127UP-ZS2P	2	1.27	2.54
B127UP-ZS3P	3	2.54	3.81
B127UP-ZS4P	4	3.81	5.08
B127UP-ZS5P	5	5.08	6.35
B127UP-ZS6P	6	6.35	7.62
B127UP-ZS7P	7	7.62	8.89
B127UP-ZS8P	8	8.89	10.16
B127UP-ZS9P	9	10.16	11.43
.....			
B127UP-ZS50P	50	(PIN-1)x1.27	(PIN)x1.27

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN®	
DIM. X X.X X.XX X.XXX GENERAL ANGLE: ±3°		TITLE: 1.27FH H4.3 2xnPin 180度 W3.0 U型 PC2.4 6T				QR CODE	
		DWG. NO.: B127UP-ZSNP		DRAWN: MAX			
		PART NO.: B127UP-ZSNP		CHECKED: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL

	A	B	C	D	E	
REV.	DESCRIPTION			ECN NO.	NAME	DATE

SPECIFICATIONS
Current Rating: 1.0 Amps
Withstanding Voltage:AC 500V
Insulation Resistance:1000MΩ Min
Contact Resistance:20mΩ Max
Operation Temperature:-40°to+105°
Insrlator Material:Polyester(UL94V-0)
Contact Material:Phosphor bronze
Standard:PA6T
Contact Plating:Gold Flash
Max.Processing Temp:240°C for30-60seconds
(260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
B127UP-ZS1P	1	0.00	1.27
B127UP-ZS2P	2	1.27	2.54
B127UP-ZS3P	3	2.54	3.81
B127UP-ZS4P	4	3.81	5.08
B127UP-ZS5P	5	5.08	6.35
B127UP-ZS6P	6	6.35	7.62
B127UP-ZS7P	7	7.62	8.89
B127UP-ZS8P	8	8.89	10.16
B127UP-ZS9P	9	10.16	11.43
.....			
B127UP-ZS50P	50	(PIN-1)x1.27	(PIN)x1.27

RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

GENERAL TOLERANCE DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD

DIM.	TOL.
X	
X.X	±0.30
X.XX	±0.25
X.XXX	±0.15
GENERAL ANGLE:	±3°

UNIT: mm SCALE: none SHEET: 1of 1 DWG. SIZE: A4 LAYER: bxconn

BXCONN®

[illegible]