





RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.


REV.	ECN. NO.	APPD.



SCHEMATIC



Mechanical




Specification

Operating Life	1,000,000
Contact rating	50mA@12V DC.
Insulation resistance	50 Ω min.
Contact resistance	100mΩ max.initial.
Dielectric Strength	250 V AC(1mm)
Travel	0.25±0.15mm

ITEM	DESCRIPTION	MATERIAL	QTY	COLOR	FINISH/COLOR
E	Cover	brass	1	Silvery white	copper- tin
D	cap	PPA	1	-	-
C	shrapnel	Stainless steel	1	-	Silver plating
B	COVER	PPA	1	Black	-
A	button	brass	1	Silvery white	Silver plating

Type	Operating Force(gf)	Height mm	Button	Leads Shape (G,J,T)	Ground pin (0,1)	Pegs Option (0,1)
YTS3R003***X	1: 100±30GF 2: 130±30GF 3: 160±30GF 4: 180±50GF 5: 250±50GF 6: 160±50GF 7: 320±80GF	R	B (Black)	G	0	0
		Q				
		P				
		D				
		N				
		M				
		L				
		K				
		J				
		I				
		H				
		G				
		F				
		E				

X. ±0.50	X.* ± 2°	UNITS mm		深圳市怡远科技有限公司				
.X ±0.30	.X* ± 1°			SHENZHEN YIYUAN TECHNOLOGY CO.,LTD				
.XX ±0.10	.XX* ± 0.5°	MAT'L 	PART NO. YTS3R003****X		TITLE: TACTILE SWITCH 6x6mm			
.XXX ± 0.05								
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD		FINISH 	APPD: ROGER		DWG NO.: YTS3R003****X			
			CHKD: RDC					
		Q'TY 	DR: BILLY WANG 2020/08/21			SCALE	SHEET	REV.
						1/1	1/1	A1