

RoHS

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance:20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40°C to +105°C

Contact Material:Brass





Contact Plating:Au Or Tin Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Dimension antitheses list								
ITEM	PA	PW	PC	L1	L2	L3	H	W
001	6.0		3.0	11.5			2.5	5.0
Alternate								

OPERATION

DRAW

SCALE

FIT

深圳市连盛精密连接器有限公司

X.X ±0.30

DRAW

UNIT

mm

X.XX ±0.20

CHECK

SIZE

A4

PART NO.

1010301437

X.XXX ±0.10

APPROVE

SHEET

1/1

TITLE:

2.54PH H=2.5 2*19P DIP PA6.0
PC3.0 L=11.5 AU0.6U PA6T

Angle ±3°

DIM TOL

PROJ.

◆

1

2

3

4

5

6

7

8

9