






3D View



(For Reference Only)
Stated At Compression

NOTES:

1:MATERIAL

1-1: SUS-304 THICKNE=0.10MM

2:SPECIFICATIONS

2-1: RATED CURRENT: 1.0A

2-2: VOLTAGE RATING: 1.5V

2-3: CONTACT RESISTANCE: 80mΩ/MAX

2-4: WELDING THRUST: ≥3KG

2-5: OPERATING TEMPERATURE: -40°C~+85°C

3:DURABILITY: 1500 CYCLES

4:SALT SPRAY TIME: 24H

5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50u" MIN


6:REQUIREMENTS

6-1:TERMINAL TO EAT FULL TIN,NOTPEELING,

WELDING OBVIOUS COLOR AND OTHED ADVERSE


6-2:ROHS,REACH,HF HALOGER ADVERSE OF DOMESTIC

AND INTERNATIONAL ENVIRONMNTAL REQUIREMENTS



RECOMMENDED PCB LAYOUT

TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)



METAL MASK T=0.08

TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)

GENERAL TOLERANCES (UNLESS SOECIFIED)

DISTANCE	ANGLE
X. ±0.30	X.* ±2.0°
.X ±0.20	.X* ±1.0°
.XX ±0.15	.XX* ±0.5°

DRAFT WHERE APPLICABLE APPROVED BY
MUST REMAIN
WITHIN DIMENSIONS

SCALE: 1:1
UNIT: MM

DRAWN BY

LUDAH

CHEVKED BY

/

LUJIAH



瑾珩精密

TITLE: 天线薄片
L3.50*W1.50*H3.55

MANUFACTURE DWG

PART NO.



TP-T0-3511

SCALE

N:A


SHEET

1:2





Customer To Use Direction

Pull Out Direction
(出料方向)





The Carrier Tape Is Heat-Sealed Packaging The Peeling Angle Of The Heat-Sealing Cover Tape Is 165°~180° And The Peeling Force Is 30~120g.



Carton Size
290*330*4 K3K

Carton Size
345*345*360 K=K



GENERAL TOLERANCES
(UNLESS SOECIFIED)

SCALE: 1:1
UNIT: MM

DISTANCE ANGLE
X. ±0.30 X.* ±2.0°
.X ±0.20 .X* ±1.0°
.XX ±0.15 .XX* ±0.5°

DRAWN BY

LUDAH

CHEVKED BY

/

DRAFT WHERE APPLICABLE APPROVED BY
MUST REMAIN
WITHIN DIMENSIONS

LUJIAH



瑾珩精密

TITLE: 天线薄片
L3.50*W1.50*H3.55

MANUFACTURE DWG

PART NO.
TP-T0-3511

SCALE

N:A

SHEET

2:2