

- NOTES:
- 1:MATERIAL
1-1: SUS-304 THICKNE=0.10MM
 - 2:SPECIFICATIONS
2-1: RATED CURRENT: 1.0A
2-2: VOLTAGE RATING: 1.5V
2-3: CONTACT RESISTANCE: 80mΩ/MAX
2-4: WELDING THRUST: ≥3KG
2-5: OPERATING TEMPERATURE: -40°C~+85°C
 - 3:DURABILITY: 1500 CYCLES
 - 4:SALT SPRAY TIME: 24H
 - 5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50μ" MIN
 - 6:REQUIREMENTS
6-1:TERMINAL TO EAT FULL TIN,NOTPEELING,
WELDING OBVIOUS COLOR AND OTHED ADVERSE
6-2:ROHS, REACH, HF HALOGER ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMNTAL REQUIREMENTS


0.90
Φ 0.10 Y

// 0.06 X



Over Pick&
Place Area

-X-

Solder Area




0.08 X




RECOMMENDED PCB LAYOUT

TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)




METAL MASK T=0.08




TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)




(For Reference Only)
Stated At Compression



GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM				
	DRAWN BY				
	LUDAH				
	CHEVKED BY				
DISTANCE ANGLE X. ±0.30 X.* ±2.0° .X ±0.20 .X* ±1.0° .XX ±0.15 .XX* ±0.5°	/		TITLE: 天线薄片 L3.50*W1.50*H4.30		
	LUJIAH		MANUFACTURE DWG		
DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS			PART NO. TP-T1-4311		
			SCALE N:A		
				SHEET 1:2	





The Carrier Tape Is Heat-Sealed Packaging The Peeling Angle Of The Heat-Sealing Cover Tape Is 165°~180° And The Peeling Force Is 30~120g.



Carton Size
290*330*4 K3K

Carton Size
345*345*360 K=K



GENERAL TOLERANCES
(UNLESS SOECIFIED)

SCALE: 1:1
UNIT: MM

DISTANCE		ANGLE
X. ±0.30	X.* ±2.0°	
.X ±0.20	.X* ±1.0°	
.XX ±0.15	.XX* ±0.5°	

DRAWN BY
LUDAH
CHEVKED BY
/

DRAFT WHERE APPLICABLE APPROVED BY
MUST REMAIN
WITHIN DIMENSIONS

LUJIAH



瑾珩精密

TITLE: 天线薄片
L3.50*W1.50*H4.30

MANUFACTURE DWG

PART NO.
TP-T1-4311

SCALE
N:A

SHEET
2:2