

A	Dept	晨翔2.54mm简牛，40PIN，镀金，直插，黑胶, 针长11.6mm				REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED	A										
	Qty					A	NEW RELEASE	JLZ 07/05/24'													
	DC	1																			
	ED	1																			
	IE	1																			
B	ISO	1									B										
	PD	1																			
	R&D	1																			
	SD	1																			
	QA	1																			
C	QC	1									C										
	QE	1																			
	晨翔料号：DS1013-40SSiB1-B-0				备注: 1. 电性说明: 1.1 接触阻抗: 20毫欧最大 1.2 耐压: 600伏交流电一分钟 1.3 绝缘阻抗: 1000兆欧最小 1.4 额定电流: 3安 2. 环境特性: 2.1 工作温度: -40~+105° C 3. 材料: 3.1 四方针: H62黄铜, 镍底镀金 3.2 胶芯: PBT, 黑色, 阻燃 4. 产品符合欧盟RoHS环保要求																
D										D											
	E										E										
F													F								
G												G									
H												H									

晨翔2.54mm简牛，40PIN，镀金，直插，黑胶, 针长11.6mm

晨翔料号：DS1013-40SSiB1-B-0

40P

48.26±0.25

2.54±0.1

0.64±0.05

0.30

8.8

58.40±0.3

2.54

48.26

2.54

1.02

PCB板孔尺寸参考
公差: ±0.05

GENERAL TOLERANCE		ANGLE TOLERANCE	
X.	±0.60	X.	±5°
.X	±0.38	.X	±3°
.XX	±0.25	.XX	±2°

DRAWING TYPE	CUSTOMER		
SCALE	1:1	SHEET	1 OF 1
DRAWING NO.	C-DS1013-XXXXX-X-X-A		

PROJECTION		TITLE	2.54mm简牛，40PIN，镀金，直插，黑胶 针长11.60mm	
UNITS	mm			
SHEET SIZE	A4	SERIES	DS1013 SERIES	

晨翔电子有限公司
CONNFLY CONNFLY ELECTRONIC CO. LTD