






3D View




Solder Area




(For Reference Only)
Stated At Compression

NOTES:

- 1:MATERIAL
1-1: SUS-304 THICKNE=0.10MM
- 2:SPECIFICATIONS
2-1: RATED CURRENT: 1.0A
2-2: VOLTAGE RATING: 1.5V
2-3: CONTACT RESISTANCE: 80mΩ/MAX
2-4: WELDING THRUST: ≥3KG
2-5: OPERATING TEMPERATURE: -40°C~+85°C
- 3:DURABILITY: 1500 CYCLES
- 4:SALT SPRAY TIME: 24H
- 5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50u" MIN
- 6:REQUIREMENTS
6-1:TERMINAL TO EAT FULL TIN,NOTPEELING,
WELDING OBVIOUS COLOR AND OTHED ADVERSE
6-2:ROHS.REACH.HF HALOGER ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMNTAL REQUIREMENTS





RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)




METAL MASK T=0.08
TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)

GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM			瑾珩精密			
	DRAWN BY						
	LUDAH						
	CHEVKED BY						
DISTANCE ANGLE		/		TITLE: 天线弹片 L2.20*W1.00*H1.10		MANUFACTURE DWG	
X. ±0.30 X.* ±2.0°		PART NO. TP-T1-1131		SCALE N:A		SHEET 1:2	
.X ±0.20 .X* ±1.0°							
.XX ±0.15 .XX* ±0.5°							
DRAFT WHERE APPLICABLE APPROVED BY		LUJIAH					
MUST REMAIN WITHIN DIMENSIONS							




Customer To Use Direction

Pull Out Direction
(出料方向)



The Carrier Tape Is Heat-Sealed
Packaging The Peeling Angle Of The
Heat-Sealing Cover Tape Is 165°~180°
And The Peeling Force Is 30~120g.



GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM		 瑾珩精密				
	DRAWN BY						
	DISTANCE ANGLE		LUDAH		TITLE: 天线排片 L2.20*W1.00*H1.10	MANUFACTURE DWG	
	X. ± 0.30 X.* $\pm 2.0^\circ$		CHECKED BY				
.X ± 0.20 .X* $\pm 1.0^\circ$		/					
.XX ± 0.15 .XX* $\pm 0.5^\circ$				PART NO.		SCALE	SHEET
DRAFT WHERE APPLICABLE APPROVED BY				TP-T1-1131		N:A	2:2
MUST REMAIN		LUJIAH					
WITHIN DIMENSIONS							