







PCB layout and Circuit Diagram



Technical parameter

技术参数

Rated value: DC24V 50mA

额定值: DC24V 50mA

Contact resistance: $\leq 50\text{m}\Omega$

接触电阻: $\leq 50\text{m}\Omega$

Insulation resistance: $\geq 10\text{M}\Omega$

绝缘电阻: $\geq 10\text{M}\Omega$

Operating temperature: $-40^\circ\text{C} \sim +160^\circ\text{C}$

使用温度: $-40^\circ\text{C} \sim 160^\circ\text{C}$

Action force: $300 \pm 50\text{gf}$

动作力: $300 \pm 50\text{gf}$

Stroke: 1.00 ± 0.2

行程: 1.00 ± 0.2

Waterproof grade: IP67

防水等级: IP67

Service life: $\geq 1,000,000$

寿命: $\geq 1,000,000$

HOUSE 底座	Nylon 尼龙	Black 黑色
ACTUATOR 按钮	Nylon 尼龙	White 白色
COVER 上盖	Nylon 尼龙	Black 黑色
CONTACT 簧片	STAINLESS STEEL 不锈钢	SLIVER PLATING 镀银
TERMINAL 端子	COPPER ALLOY 铜合金	
LED		Red 红色
Name 名称	Texture of material 材质	Remarks 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP18012301040
DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
ROC CPU TECHNOLOGY CO.,LTD				
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission				