






1		2		3		4		5		6		7		8																																																																										
A	Dept	晨翔2.54mm拨码开关, 6PIN, 插板, 黑色胶芯, 白色推钮, 红色盖子, 端子镀金								REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED	A																																																																									
	Qty									A	NEW RELEASE	JLZ 07/13/24'																																																																												
	DC	1																																																																																						
	ED	1																																																																																						
B	IE	1													B																																																																									
	ISO	1																																																																																						
	PD	1																																																																																						
	R&D	1																																																																																						
C	SD	1													C																																																																									
	QA	1																																																																																						
	QC	1																																																																																						
	QE	1																																																																																						
D	晨翔料号: DS1040-06RN															备注: 1. 电性说明: 1.1 接触阻抗: 100毫欧最大 1.2 耐压: 500伏交流电一分钟 1.3 绝缘阻抗: 100兆欧最小 1.4 额定电流: 25毫安 1.5 额定电压: 24V DC 2. 环境特性: 2.1 工作温度: -40~+85° C 3. 材料: 3.1 端子: 磷铜, 镍底镀金 3.2 胶芯、盖子及推钮: PBT, 黑色、红色、白色																																																																								
E	  PCB孔位布局参考 公差: ±0.05    电路图																																																																																							
F	<table><tr><td colspan="4">GENERAL TOLERANCE</td><td colspan="4">ANGLE TOLERANCE</td><td colspan="2">PROJECTION</td><td></td><td colspan="2">TITLE</td></tr><tr><td colspan="4">X. ±0.60 .X ±0.38 .XX ±0.25</td><td colspan="4">X. ±5° .X ±3° .XX ±2°</td><td colspan="2">UNITS</td><td colspan="2">mm</td></tr><tr><td colspan="4">DRAWING TYPE</td><td colspan="4">CUSTOMER</td><td colspan="2">SHEET SIZE</td><td colspan="2">A4</td></tr><tr><td colspan="4">SCALE</td><td colspan="2">1:1</td><td colspan="2">SHEET</td><td colspan="2">1 OF 1</td><td colspan="2">SERIES</td><td colspan="2">DS1040 SERIES</td></tr><tr><td colspan="4">DRAWING NO.</td><td colspan="4">C-DS1040-XXXXX-A</td><td colspan="6" rowspan="2"> 晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD</td></tr><tr><td colspan="4"></td><td colspan="4"></td></tr></table>															GENERAL TOLERANCE				ANGLE TOLERANCE				PROJECTION			TITLE		X. ±0.60 .X ±0.38 .XX ±0.25				X. ±5° .X ±3° .XX ±2°				UNITS		mm		DRAWING TYPE				CUSTOMER				SHEET SIZE		A4		SCALE				1:1		SHEET		1 OF 1		SERIES		DS1040 SERIES		DRAWING NO.				C-DS1040-XXXXX-A				 晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD													
																GENERAL TOLERANCE				ANGLE TOLERANCE				PROJECTION			TITLE																																																													
																X. ±0.60 .X ±0.38 .XX ±0.25				X. ±5° .X ±3° .XX ±2°				UNITS		mm																																																														
																DRAWING TYPE				CUSTOMER				SHEET SIZE		A4																																																														
SCALE				1:1		SHEET		1 OF 1		SERIES		DS1040 SERIES																																																																												
DRAWING NO.				C-DS1040-XXXXX-A				 晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD																																																																																
G																G																																																																								
H																H																																																																								