


REV.	ECN.NO.	MODIFY.CONTENT	DATE



Model	L.VaR	DIM.L	W.VaR	DIM.W	H.VaR	DIM.H
DY-CCS-010101	01	1.0	01	1.0	01	1.0
DY-CCS-020202	02	1.5	02	1.5	02	1.5
DY-CCS-030303	03	2.0	03	2.0	03	2.0
DY-CCS-040404	04	2.5	04	2.5	04	2.5
DY-CCS-050505	05	3.0	05	3.0	05	3.0
DY-CCS-060606	06	3.5	06	3.5	06	3.5
DY-CCS-070707	07	4.0	07	4.0	07	4.0
DY-CCS-080808	08	4.5	08	4.5	08	4.5
DY-CCS-090909	09	5.0	09	5.0	09	5.0
.....
DY-CCS-909090	90	(90-1)x0.5+6	90	(90-1)x0.5+3	90	(90-1)x0.5+1

1. 材质:黄铜, 厚度:1.0mm±0.02mm;
2. 表面处理:镀镍;
3. 在常温常湿环境下保质期为90天
4. 未注公差:±0.1mm;
5. 盐雾试验:24小时;
6. 符合RoHS、REACH环保要求;
7. 包装方式:散装(01) 编带(02)

GENERAL TOLERANCE		FILE.NO.	DRAWN		Bob	比例	SCALE
X.±0.25	x.*±5°	TITLE	CHECKED		Adam	单位	
.X±0.20	.x.*±2°		PART.NO.	APPROVED		Dylan	mm
.XX±0.15	.xx.*±1°	导电铜片		DATE			
.XXX±0.05	.xxx.*±0.5°	REV.	德砚电子		深圳市德砚电子有限公司 Shenzhen Deyan Electronics Co., Ltd		
SHEET	1/1	Q'TY	A/0				