

3D View

NOTES:

1:MATERIAL

1-1: SUS-301 THICKNE=0.10MM

2:SPECIFICATIONS

2-1: CONTACT RESISTANCE: 80mΩ/MAX

2-2: RATED CURRENT: 1.0A

2-3: VOLTAGE RATING: 1.5V

2-4: WELDING THRUST: ≥3KG

2-5: OPERATING TEMPERATURE: -40°C~+85°C

3:DURABILITY: 1500 CYCLES







4:SALT SPRAY TIME: 24H

5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50u" MIN

6:REQUIREMENTS

6-1:TERMINAL TO EAT FULL TIN,NOTPEELING,
WELDING OBVIOUS COLOR AND OTHED ADVERSE

6-2:ROHS, REACH, HF HALOGER ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMNTAL REQUIREMENTS



(For Reference Only)
Stated At Compression



RECOMMENDED PCB LAYOUT

TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)

METAL MASK T=0.08


TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)

GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM		 瑾珩精密		
	DISTANCE ANGLE	DRAWN BY			
	X. ±0.30 X.* ±2.0°	LUDAH			
	.X ±0.20 .X* ±1.0°	CHEVKED BY			
	.XX ±0.15 .XX* ±0.5°	/			
DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS			TITLE: 天线薄片 L2.90*W1.00*H1.25	MANUFACTURE DWG	
			PART NO. TP-T1-1211	SCALE N:A	SHEET 1:2
	LUJIAH				




Customer To Use Direction

Pull Out Direction
(出料方向)





The Carrier Tape Is Heat-Sealed
Packaging The Peeling Angle Of The
Heat-Sealing Cover Tape Is 165°~180°
And The Peeling Force Is 30~120g.



Carton Size
290*330*4 K3K

Carton Size
345*345*360 K=K



GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM		 瑾珩精密		
	DRAWN BY LUDAH				
DISTANCE ANGLE X. ±0.30 X.* ±2.0° .X ±0.20 .X* ±1.0° .XX ±0.15 .XX* ±0.5°	CHECKED BY /		TITLE: 天线排片 L2.90*W1.00*H1.25		MANUFACTURE DWG
	DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS				
	LUJIAH		PART NO. TP-T1-1211		SCALE N:A