






3D View



NOTES:

1:MATERIAL

1-1: SUS-304 THICKNE=0.10MM

2:SPECIFICATIONS

2-1: RATED CURRENT: 1.0A

2-2: VOLTAGE RATING: 1.5V

2-3: CONTACT RESISTANCE: 80mΩ/MAX

2-4: WELDING THRUST: ≥3KG

2-5: OPERATING TEMPERATURE: -40°C~+85°C


3:DURABILITY: 1500 CYCLES

4:SALT SPRAY TIME: 24H

5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50u" MIN


6:REQUIREMENTS

6-1:TERMINAL TO EAT FULL TIN,NOTPEELING,
WELDING OBVIOUS COLOR AND OTHED ADVERSE
6-2:ROHS.REACH.HF HALOGER ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMNTAL REQUIREMENTS



RECOMMENDED PCB LAYOUT



TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)



METAL MASK T=0.08


TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)

GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM			瑾珩精密					
	DRAWN BY								
	LUDAH								
	CHEVKED BY								
DISTANCE ANGLE		/		TITLE: 天线薄片 L3.50*W1.50*H2.50	MANUFACTURE DWG				
X. ±0.30 X* ±2.0°		LUDAH							
.X ±0.20 .X* ±1.0°		CHEVKED BY		SCALE		SHEET			
.XX ±0.15 .XX* ±0.5°		/							
DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS		LUJIAH		PART NO. TP-T1-2521		N:A		1:2	



Customer To Use Direction


Pull Out Direction
(出料方向)



Heat seal
and self-adhesive



The Carrier Tape Is Heat-Sealed
Packaging The Peeling Angle Of The
Heat-Sealing Cover Tape Is 165°~180°
And The Peeling Force Is 30~120g.

The Carrier Tape Is Cold-Sealed
And The Peeling Angle Of The
Cold-Sealing Cover Tape Is 165°~180°.



Carton Size
290*330*4 K3K

Carton Size
345*345*360 K=K



GENERAL TOLERANCES
(UNLESS SOECIFIED)

SCALE: 1:1
UNIT: MM

DISTANCE ANGLE
X. ±0.30 X.* ±2.0°
.X ±0.20 .X* ±1.0°
.XX ±0.15 .XX* ±0.5°

DRAWN BY

LUDAH

CHEVKED BY

/

DRAFT WHERE APPLICABLE APPROVED BY
MUST REMAIN
WITHIN DIMENSIONS

LUJIAH



瑾珩精密

TITLE: 天线薄片
L3.50*W1.50*H2.50

MANUFACTURE DWG

PART NO.
TP-T1-2521

SCALE
N:A

SHEET
2:2