

3D View

NOTES:

1:MATERIAL

1-1: SUS-301 THICKNE=0.10MM

2:SPECIFICATIONS

2-1: RATED CURRENT: 1.0A

2-2: VOLTAGE RATING: 1.5V

2-3: CONTACT RESISTANCE: 80mΩ/MAX

2-4: WELDING THRUST: ≥3KG

2-5: OPERATING TEMPERATURE: -40°C~+85°C

3:DURABILITY: 1500 CYCLES




4:SALT SPRAY TIME: 24H

5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50u" MIN


6:REQUIREMENTS

6-1:TERMINAL TO EAT FULL TIN,NOTPEELING,
WELDING OBVIOUS COLOR AND OTHER ADVERSE

6-2:ROHS.REACH.HF HALOGER ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMNTAL REQUIREMENTS




(For Reference Only)
Stated At Compression




RECOMMENDED PCB LAYOUT


TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)





METAL MASK T=0.08

TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)




GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM		
	DRAWN BY LUDAH		
DISTANCE ANGLE X. ±0.30 X.* ±2.0° .X ±0.20 .X* ±1.0° .XX ±0.15 .XX* ±0.5°	CHEVKED BY /	TITLE: 天线薄片 L1.90*W1.00*H2.30	
	DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS	PART NO. TP-T1-2311	MANUFACTURE DWG
	LUJIAH	SCALE N:A	SHEET 1:2




Customer To Use Direction

Pull Out Direction

(出料方向)






The Carrier Tape Is Heat-Sealed Packaging The Peeling Angle Of The Heat-Sealing Cover Tape Is 165°~180° And The Peeling Force Is 30~120g.



Carton Size
290*330*4 K3K

Carton Size
345*345*360 K=K



GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM		<div> 瑾珩精密</div>					
	DRAWN BY					TITLE: 天线排片 L1.90*W1.00*H2.30	MANUFACTURE DWG	
	LUDAH							
	CHEVKED BY							
DISTANCE ANGLE		/		PART NO.		SCALE	SHEET	
X. ±0.30	X.* ±2.0°			TP-T1-2311		N:A	2:2	
.X ±0.20	.X* ±1.0°							
.XX ±0.15	.XX* ±0.5°							
DRAFT WHERE APPLICABLE APPROVED BY		LUJIAH						
MUST REMAIN								
WITHIN DIMENSIONS								