





3D View



NOTES:

1:MATERIAL

1-1: SUS-301 THICKNE=0.06MM

2:SPECIFICATIONS

2-1: RATED CURRENT: 1.0A

2-2: VOLTAGE RATING: 1.5V

2-3: CONTACT RESISTANCE: 80MΩ/MAX

2-4: WELDING THRUST: >3KG

2-5: OPERATING TEMPERATURE: -40°C~+85°C

3:DURABILITY: 1500 CYCLES



4:SALT SPRAY TIME: 24H

5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50μ" MIN

6:REQUIREMENTS


6-1:TERMINAL TO EAT FULL TIN,NOTPEELING,
WELDING OBVIOUS COLOR AND OTHER ADVERSE

6-2:ROHS, REACH, HF HALOGER ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMNTAL REQUIREMENTS



RECOMMENDED PCB LAYOUT

TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)



METAL MASK T=0.08

TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)

GENERAL TOLERANCES
(UNLESS SOECIFIED)

DISTANCE	ANGLE
X. ±0.30	X.* ±2.0°
.X ±0.20	.X* ±1.0°
.XX ±0.15	.XX* ±0.5°

DRAFT WHERE APPLICABLE APPROVED BY
MUST REMAIN
WITHIN DIMENSIONS

SCALE: 1:1
UNIT: MM

DRAWN BY

LUDAH

CHEVKED BY

/

LUJIAH



瑾珩精密

TITLE: 规格书

L2.50*W1.00*H0.80

MANUFACTURE DWG

PART NO.

TP-T1-0811

SCALE

N:A

SHEET

1:2

A

B

C



D

A



B

C


D



The Carrier Tape Is Heat-Sealed Packaging The Peeling Angle Of The Heat-Sealing Cover Tape Is $165^{\circ}\sim180^{\circ}$ And The Peeling Force Is 30~120g.





20Reel



Carton Size
290*330*4 K3K

Carton Size
345*345*360 K=K



GENERAL TOLERANCES (UNLESS SOECIFIED)		SCALE: 1:1 UNIT: MM		 瑾珩精密	
DISTANCE ANGLE		DRAWN BY			
X. ± 0.30 X.* $\pm 2.0^{\circ}$		LUDAH		TITLE: 无规格 L2.50*W1.00*H0.80	
.X ± 0.20 .X* $\pm 1.0^{\circ}$		CHEVKED BY			
.XX ± 0.15 .XX* $\pm 0.5^{\circ}$		/		MANUFACTURE DWG	
DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS					
		LUJIAH		PART NO. TP-T1-0811	
				SCALE N:A	
				SHEET 2:2	