

1		2		3		4		5		6		7		8																																																															
A	Dept	晨翔2.54mm简牛, 50PIN, 镀金, 直插, 黑胶, 针长11.6mm								REV.	DESCRIPTION		DRAWN		CHECKED		APPROVED																																																												
	Qty									A	NEW RELEASE		JLZ 07/05/24'																																																																
	DC	1																																																																											
	ED	1																																																																											
	IE	1																																																																											
	ISO	1																																																																											
B	PD	1																																																																											
	R&D	1																																																																											
	SD	1																																																																											
	QA	1																																																																											
	QC	1																																																																											
	QE	1																																																																											
C										备注: 1. 电性说明: 1.1 接触阻抗: 20毫欧最大 1.2 耐压: 600伏交流电一分钟 1.3 绝缘阻抗: 1000兆欧最小 1.4 额定电流: 3安 2. 环境特性: 2.1 工作温度: -40~+105° C 3. 材料: 3.1 四方针: H62黄铜, 镍底镀金 3.2 胶芯: PBT, 黑色, 阻燃 4. 产品符合欧盟RoHS环保要求																																																																			
D																																																																													
E																																																																													
F																																																																													
G		PCB孔位尺寸参考 公差: ±0.05																																																																											
H		<table><tr><td colspan="2">GENERAL TOLERANCE</td><td colspan="2">ANGLE TOLERANCE</td><td colspan="2">PROJECTION</td><td colspan="2">TITLE</td><td colspan="2">2.54mm简牛, 50PIN, 镀金, 直插, 黑胶 针长11.60mm</td></tr><tr><td>X.</td><td>±0.60</td><td>X.</td><td>±5°</td><td colspan="2">mm</td><td colspan="2"></td><td colspan="2"></td></tr><tr><td>.X</td><td>±0.38</td><td>.X</td><td>±3°</td><td colspan="2">A4</td><td colspan="2">SERIES</td><td colspan="2">DS1013 SERIES</td></tr><tr><td>.XX</td><td>±0.25</td><td>.XX</td><td>±2°</td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td></tr><tr><td colspan="2">DRAWING TYPE</td><td colspan="2">CUSTOMER</td><td colspan="2">SCALE</td><td colspan="2">1:1</td><td colspan="2">SHEET 1 OF 1</td></tr><tr><td colspan="2">DRAWING NO.</td><td colspan="2">C-DS1013-XXXXX-A</td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td></tr></table>								GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE		2.54mm简牛, 50PIN, 镀金, 直插, 黑胶 针长11.60mm		X.	±0.60	X.	±5°	mm						.X	±0.38	.X	±3°	A4		SERIES		DS1013 SERIES		.XX	±0.25	.XX	±2°							DRAWING TYPE		CUSTOMER		SCALE		1:1		SHEET 1 OF 1		DRAWING NO.		C-DS1013-XXXXX-A								晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD							
GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE		2.54mm简牛, 50PIN, 镀金, 直插, 黑胶 针长11.60mm																																																																					
X.	±0.60	X.	±5°	mm																																																																									
.X	±0.38	.X	±3°	A4		SERIES		DS1013 SERIES																																																																					
.XX	±0.25	.XX	±2°																																																																										
DRAWING TYPE		CUSTOMER		SCALE		1:1		SHEET 1 OF 1																																																																					
DRAWING NO.		C-DS1013-XXXXX-A																																																																											