




REV	ECN NO.	APPD
A	HG-17-0091	PRJ0J0M

规格 Specifications


额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	详见左下：操作力度
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.18±0.05mm
包装数量 Package	4000PCS/Reel



RECOMMENDED P.C.B. LAYOUT

安装尺寸图

CIRCUIT DIAGRAM
回路图



PRODUCT NO. : 1TS004E*****A1 - CT

轻触开关
3X3系列
外形：
E=铜头平脚带盖贴膜

材质：
0=初始材质
I=新增材质
依次增加

产品高度(H)：
150=1.5mm
200=2.0mm
250=2.5mm
300=3.0mm

操作力度：
160=160±40gf
250=250±50gf

手感：
0=常規

编带
非编带，不启用

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
6	按钮	1	C2680	黄色
5	盖板	1	SUS	/
4	防尘膜	1	PT	黄色
3	弹片	2	SUS	镀银
2	底座	1	LCP	灰色
1	卡件	1	C5191	镀银

X. ± 0.3	X' ± 3'	UNITS	MM
X ± 0.2	X' ± 2'	MAT'L	
.XX ± 0.1	.XX' ± 1'		
.XXX ± 0.05	.XXX' ± 0.5'	FINISH	

NAME(INTENDED USE) 3X3 SERIES TACT SWITCH	HON YUAN HON YUAN PRECISION IND. CO.,LTD. SHENZHEN, CHINA.
PART NO.(INTENDED USE) 1TS004E-1600-1500A1-CT	TITLE: PRODUCT DRAWING
APPD: W.P.Lu 2017.12.07	DWG NO.: 1TS004E-1600-1500A1-CT
CHKD: S.L.Li 2017.12.07	SCALE SHEET REV.
DR: Y.Y.Chen 2017.12.07	18/1 1/1 A

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.