


REV	ECN NO.	APPD
A	HR-24-0032	ZO



规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	250±50gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.15±0.1mm
包装数量 Package	2500PCS/Reel



RECOMMENDED P.C.B. LAYOUT

安装尺寸图



CIRCUIT DIAGRAM

回路图

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
6	TERMINAL	1	PHOSPHOR BRONZE	Ag-PLATED
5	HOUSING	1	PA6T	/
4	DOME	1	STAINLESS STEEL	Ag-PLATED
3	PE-FILE	1	POLYIMIDE	/
2	COVER	1	STAINLESS STEEL	NICKEL TIN
1	ACTUATOR	1	PA46	/

X. ± 0.3	X' ± 3'	UNITS	NAME(INTENDED USE)	APPD:	DWG NO.:
X. ± 0.2	X' ± 2'	MAT'L	3X4.5 TACT SWITCH	W.P.Lu 2024-03-09	1TS036A-2500-1700A7-CT
XX ± 0.1	XX' ± 1'		PART NO.(INTENDED USE)	CHKD: S.Li 2024-03-09	SCALE SHEET
.XXX ± 0.05	.XXX' ± 0.5'	FINISH	1TS036A-2500-1700A7	DR: K.Ding 2024-03-09	REV.
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. ANY REPRODUCTION OR USE IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.					