

额定负荷	Rating	DC 12V/50mA
接触电阻	Contact Resistance	100mΩ max.
绝缘电阻	Insulation resistance	DC100V 60S 100MΩ min.
抗电强度	Dielectric strength	AC250V(50~60HZ) 60S min.
操作力	Operation force	180±40gf
寿命试验	Operating Life	100,000 cycles
行程	Travels	0.15±0.1mm
包装数量	Package	2500PCS/Reel



回路図

X. ± 0.3		UNITS	NAME(INTENDED USE)	HON YUAN HON YUAN PRECISION IND. CO.,LTD. SHENZHEN, CHINA.
X. ± 0.2				
.XX ± 0.1		MM	3X4.5 TACT SWITCH	TITLE:
.XX ± 1"				
XXX ± 0.05		FINISH	PART NO.(INTENDED USE)	PRODUCT DRAWING
.XXX ± 0.5"			1TS036A-1800-1700A7	

HON YUAN PRECISION IND. CO., LTD.
SHENZHEN, CHINA.

DWG NO.:

SCALE	SHEET	REV
-------	-------	-----

	10/1	1/1	A
---	------	-----	---