




规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC:100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50-60HZ) 60S min.
操作力 Operation force	250±50gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.18±0.1mm
包装数量 Package	4000PCS/Reel

RECOMMENDED P.C.B. LAYOUT

安装尺寸图

PRODUCT NO.: 1TS029C*****A9-CT

轻触开关

3.0×2.5系列

外形:

C=两脚直脚

按钮颜色:
底座颜色:
盖板颜色:

初始颜色, 则不启用

材质:

0=初始材质

编织带
非编织带, 不启用

产品高度 (H):

150=1.50mm

手感:

0=常规

操作力度:

250=250gf

6	ACTUATOR	1	LCP	BLACK
5	COVER	1	SUS	/
4	PE-FILE	1	PI	YELLOW
3	DOME	2	SUS	Ag-PLATED
2	HOUSING	1	LCP	WHITE
1	TERMINAL	1	PHOSPHOR COPPER	Ag-PLATED
ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
X. ± 0.3	X* ± 3'	UNITS	MM	
.X ± 0.2	.X' ± 2'	MAT'L		
.XX ± 0.1	.XX' ± 1'			
.XXX ± 0.05	.XXX' ± 0.5'	FINISH		
NAME(INTENDED USE)		HON YUAN		
TACT SWITCH		HON YUAN PRECISION IND. CO.,LTD.		
PART NO.(INTENDED USE)		SHENZHEN, CHINA.		
TITLE:		PRODUCT DRAWING		
APPD:		DWG NO.:		
W.P.Lu 2024/1/10		1TS029C-2500-1500A9-CT		
CHKD:		SCALE		
S.L.Ui 2024/1/10		SHEET		
DR:		REV.		
K.DING 2024/1/10		10/1		
		1/1		
		A		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED, OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN