

RoHS

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:500V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40°c to +105°c


Contact Material:Brass

Contact Plating:Au or Sn Over Ni




Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 5 seconds)



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE ± 0.05)



Dimension antitheses list							
ITEM	PA	PB	PC	L短	L长	H	W
001	4.0	5.4	2.80	10.50	14.50	2.0	4.0
Alternate							

				OPERATION		DRAW			SCALE	FIT	深圳市连盛精密连接器有限公司		
				X.X	±0.30					UNIT			mm
				X.XX	±0.20	CHECK			SIZE	A4			
A0	2012.04.11	NEW DRAWING		X.XXX	±0.10	APPROVE			SHEET	1/1	PART NO.	1010200688	
REV	DATE	MODIFICATION DESCRIPTION		CHANGE	Angle		±3°			PROJ.		TITLE:	2.0PH H=2.0 2*12P 正弯 PA4.0 PB5.4 PC2.8 L=10.5/14.5 AU0.6U PA6T
					DIM		TOL						