







CIRCUIT DIAGRAM

回路图


规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
机电强度 Dielectric strength	AC250V(50-60HZ) 60S min.
操作力 Operation force	160±50gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.20±0.1mm
包装数量 Package	3000PCS/Reel



RECOMMENDED P.C.B. LAYOUT

安装尺寸图



PRODUCT NO.: 1TS003D*****AA - CT

轻触开关 2X4系列 外形: A=单层全包 B=单层带柱 C=单层不带柱 D=双层全包

按钮颜色: 底座颜色: 盖板颜色: 材料: 0=初始材质 1=新增材质 依次增加

操作力度: 手感: 产品高度(H): 初始颜色 则不启用 160=160gf 180=180gf 200=200gf 250=250gf 0=带规 352=3.52mm

非带带, 不启用

7	ACTUATOR	1	PA46	BLACK
6	COVER	1	PHOSPHOR BRONZE	Ag-PLATED
5	I/M COVER	1	LCP	WHITE
4	PE-FILE	1	PE	YELLOW
3	DOME	2	STAINLESS STEEL	Ag-PLATED
2	HOUSING	1	LCP	BLACK
1	TERMINAL	1	PHOSPHOR BRONZE	Ag-PLATED
ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
NAME(INTENDED USE)		2X4 SERIES	HON YUAN	
TACT SWITCH		HON YUAN PRECISION IND. CO.,LTD.		
PART NO.(INTENDED USE)		SHENZHEN, CHINA.		
TITLE:		PRODUCT DRAWING		
APPD: ZD 2019-11-6		DWG NO.: 1TS003D-1600-3520AA-CT		
CHKD: MHLI 2019-11-6		SCALE SHEET REV.		
DR: Y.Y.Chen 2019-11-6		15/1 1/1 A		