




规格 Specifications

额定负荷 Rating	DC 12V/50mA	
接触电阻 Contact Resistance	100mΩ max.	
绝缘电阻 Insulation resistance	DC:100V 60S 100MΩ min.	
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.	
操作力 Operation force	160±40gf	180±40gf 250±50gf
寿命试验 Operating Life	100,000 cycles	
行程 Travels	0.20±0.1mm	
包装数量 Package	3000PCS/Reel	



RECOMMENDED PCB LAYOUT

安装尺寸图

CIRCUIT DIAGRAM

回路图

PRODUCT NO.: 1TS008B*****A1 - CT

轻触开关

3X4立式小龟系列

外形:

按钮颜色:

底座颜色:

盖板颜色:

操作力度:

160=180gf

180=180gf

250=250gf

手感:

0=常规

1=大手感

2=小手感

材料:

0=初始材料

1=新增材料

依次增加

编带

非编带, 不启用

产品高度 (H):

180=1.80mm

200=2.00mm

250=2.50mm

THESE DIMENSIONS AND SPECIFICATIONS ARE FOR INFORMATION ONLY. THE INFORMATION HEREIN IS NOT TO BE USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.										UNITS MM		NAME(INTENDED USE) 3X4 SERIES TACT SWITCH		PART NO.(INTENDED USE) 1TS008B-2500-2500A1		TITLE: PRODUCT DRAWING		DWG NO.: 1TS008B-2500-2500A1-CT		SCALE		SHEET		REV.	
X. ± 0.3		X. ± 0.2		X. ± 0.1		.XXX ± 0.05		FINISH		QTY		DR: Y.Y.Chen 5/9/2020		CHKD: M.H.LI 5/9/2020						12/1		1/1		A	