





REV	ECN NO.	APPD
A	HG-17-0021	PRJ0J0M

规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50-60HZ) 60S min.
操作力 Operation force	160±40gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.25±0.1mm
包装数量 Package	1000PCS/袋



CIRCUIT DIAGRAM



PRODUCT NO. : 1TS005D*****AB - CT

接触开关

外形:

按钮颜色:

底座颜色:

盖板颜色:

操作力度:

手感:

材料:

非编带

产品高度 (H):

ITEM	PART NAME	QTY	MATERIAL	FINISH
5	TERMINAL	1	H62Y	Ag-PLATED
4	HOUSING	1	PPA	BLACK
3	DOME	1	Stainless Steel	Ag-PLATED
2	COVER	1	BRASS	Sn-PLATED
1	ACTUATOR	1	PPA	BLACK

UNITS	MM	NAME(NTENDED USE)	HON YUAN
MAT'L		6X6 T/H SERIES TACT SWITCH	HON YUAN PRECISION IND. CO.,LTD.
FINISH		PART NO.(NTENDED USE)	SHENZHEN, CHINA.
Q'TY		1TS005D-1600-7000AB	PRODUCT DRAWING
		APPD: W.P.Lu 2017.1.12	DWG NO.: 1TS005D-1600-7000AB
		CHKD: S.L.Li 2017.1.12	SCALE SHEET REV.
		DR: Y.Y.Chen 2017.1.12	10/1 1/1 A