





REV	ECN NO.	APPD
A	HR-17-0021	PRLOJOM

规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50-60HZ) 60S min.
操作力 Operation force	250±50gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.25±0.1mm
包装数量 Package	1000PCS/袋



CIRCUIT DIAGRAM



PRODUCT NO. : 1TS005D*****AB - CT

轻触开关

6X6系列

外形:

按钮颜色:

底座颜色:

盖板颜色:

操作力度:

160=160gf

260=260gf

初始颜色, 则不启用

材料:

0=初始材料

1=新槽材料

依次增加

产品高度(H):

430=4.30mm

500=5.00mm

600=6.00mm

700=7.00mm

800=8.00mm

900=9.00mm

手感:

0=常规

1=大于手感

2=小于手感

3=特殊手感

非编带

0=初始材料

1=新槽材料

依次增加

ITEM	PART NAME	QTY	MATERIAL	FINISH
5	TERMINAL	1	H62Y	Ag-PLATED
4	HOUSING	1	PPA	BLACK
3	DOME	1	Stainless Steel	Ag-PLATED
2	COVER	1	BRASS	Sn-PLATED
1	ACTUATOR	1	PPA	BLACK
1	PART NAME	QTY	MATERIAL	FINISH

X. ± 0.3	X' ± 3'
X ± 0.2	X' ± 2'
.XX ± 0.1	.XX' ± 1'
.XXX ± 0.05	.XXX' ± 0.5'

NAME(NTENDED USE)	6X6 T/H SERIES	TACT SWITCH
PART NO.(NTENDED USE)	1TS005D-2500-7000AB	
APPD:	W.P.Lu 2017.1.12	
CHKD:	S.L.Ji 2017.1.12	
DR:	Y.Y.Chen 2017.1.12	

DWG NO.:	1TS005D-2500-7000AB
SCALE	10/1
SHEET	1/1
REV.	A

HON YUAN

HON YUAN PRECISION IND. CO.,LTD.

SHENZHEN, CHINA.

PRODUCT DRAWING

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED, OR IN ANY MANNER DISCLOSED TO THE PUBLIC WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.