





REV	ECN NO.	APPD
A	HG-17-0025	PRJ0J0M

规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50-60HZ) 60S min.
操作力 Operation force	160±40gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.25±0.1mm
包装数量 Package	1000PCS/袋



CIRCUIT DIAGRAM



PRODUCT NO. : 1TS005D*****AB - CT

接触开关

外形:

按钮颜色:

底座颜色:

盖板颜色:

操作力度:

手感:

材料:

产品高度 (H):

非编带

ITEM	PART NAME	QTY	MATERIAL	FINISH
5	TERMINAL	1	H62Y	Ag-PLATED
4	HOUSING	1	PPA	BLACK
3	DOME	1	Stainless Steel	Ag-PLATED
2	COVER	1	BRASS	Sn-PLATED
1	ACTUATOR	1	PPA	BLACK
1	PART NAME	QTY	MATERIAL	FINISH

X. ± 0.3	X' ± 3'
.X ± 0.2	.X' ± 2'
.XX ± 0.1	.XX' ± 1'
.XXX ± 0.05	.XXX' ± 0.5'

NAME(NTENDED USE) 6X6 T/H SERIES TACT SWITCH	HON YUAN HON YUAN PRECISION IND. CO.,LTD. SHENZHEN, CHINA.
PART NO.(NTENDED USE) 1TS005D-1600-9000AB	PRODUCT DRAWING
APPD: W.P.Lu 2017.1.12	DWG NO.: 1TS005D-1600-9000AB
CHKD: S.L.Li 2017.1.12	SCALE SHEET REV.
DR: Y.Y.Chen 2017.1.12	10/1 1/1 A

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED, OR IN ANY MANNER TRANSMITTED WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.