








规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50-60Hz) 60S min.
操作力 Operation force	250±50gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.15±0.1mm
包装数量 Package	2000PCS/Reel



P.C.B LAYOUT

PRODUCT NO.: 1TS022A***-3500A3-CT

- 轻触开关
4. 5X3.35 系列
- 外形:
- 按钮颜色:
- 底座颜色:
- 盖板颜色:
- 初始颜色, 则不启用
- 操作力度:
- 160=160gf
- 250=250gf
- 手感:
- 0=常规
- 1=大手感
- 2=小手感
- 3=特殊手感
- 材料:
- 0=初始材料
- 1=新增材料
- 依次增加
- 产品高度(H):
- 350=3.50mm
- 非编带, 不启用

5	ACTUATOR	1	LCP	WHITE
4	COVER	1	磷铜	Ag-PLATED
3	DOME	2	SUS301	Ag-PLATED
2	HOUSING	1	LCP	BLACK
1	TERMINAL	3	磷铜	Ag-PLATED
ITEM	PART NAME	QUANTITY	MATERIAL	FINISH

X. ± 0.3	X' ± 3'	UNITS	MM	NAME(INTENDED USE)	HON YUAN
X ± 0.2	X' ± 2'	MAT'L		4.5X3.4	HON YUAN PRECISION IND. CO.,LTD.
.XX ± 0.1	.XX' ± 1'			TACT SWITCH	SHENZHEN, CHINA.
.XXX ± 0.05	.XXX' ± 0.5'	FINISH		PART NO.(INTENDED USE)	TITLE:
				1TS022A-2500-3500A3-CT	PRODUCT DRAWING
				APPD: W.P.LU 2023-12-11	DWG NO.:
				CHKD: S.L.Li 2023-12-11	1TS022A-2500-3500A3-CT
				DR: K.Ding 2023-12-11	SCALE
					10/1
					1/1
					REV.
					A