





RoHS

NOTES:

- 1.Rated voltage : 250V(Max)
- 2.Current Rating: 3.0 AMP (Max.)
- 3.Contact Resistance: 30mΩ (Max.)
- 4.Withstanding voltage : 1000V AC/Minute
- 5.Insulation Resistance: 1000MΩ (Min)
- 6.Operation Temperature: -40℃ to +105℃

MATERIAL:

- 1.Housing : PBT (UL94V-0)
- 2.Contact : Copper Alloy, Au/Sn over Ni Plating
- 3.Shell : Steel, Ni Plated
- 4.Screw : SWRCH, Ni Plated
- 5.Harpoon : Copper Alloy, Tin Plated



Recommended P. C. B Layout
Top View
Tolerance: ±0.05mm

Ordering Information

6235-02 M 37 XX S X A XX

Connector Type: F=Female, M=Male
No. of Pins: 9, 15, 25, 37P
Contact: S0:Gold Flash/Tin, G0:Gold Flash, G2:2u" Gold, G3:3u" Gold, G4:5u" Gold
Plating: S0:Gold Flash/Tin, G0:Gold Flash, G2:2u" Gold, G3:3u" Gold, G4:5u" Gold
Color: B=Black, W=White, U=Blue
Packing: A=Tray
Serial code: XX

DRAW		OPERATION		SCALE	FIT	JILN ® 东莞市锦凌电子有限公司 DONGGUAN JINLING ELECTRONIC CO., LTD	
		X.X	±0.30	UNIT	mm		
CHECK		X.XX	±0.20	SIZE	A4	PART NO.	6235-02M37XXSXAXX
		X.XXX	±0.10	SHEET	1/1	TITLE:	DP-37P公/铆鱼叉锁螺丝
APPROVE		Angle	±3°	PROJ.			