

RoHS

NOTES:





- 1.Rated voltage : 250V(Max)
- 2.Current Rating: 3.0 AMP (Max.)
- 3.Contact Resistance: 30mΩ (Max.)
- 4.Withstanding voltage : 1000V AC/Minute
- 5.Insulation Resistance: 1000MΩ (Min)
- 6.Operation Temperature: -40℃ to +105℃

MATERIAL:

- 1.Housing : PBT (UL94V-0)
- 2.Contact : Copper Alloy, Au/Sn over Ni Plating
- 3.Shell : Steel, Ni or Sn Plated
- 4.Screw : SWRCH, Ni Plated
- 5.Harpoon : SPCC, Tin Plated

Ordering Information

6235-03	F	15	XX	R	X	A	XX
Connector Type	No. of Pins	Contact Plating	Color	Packing	Serial code		
F=Female M=Male	09,15, 25,37P	S0:Gold Flash/Tin G0:Gold Flash G2:2u" Gold G3:3u" Gold G4:5u" Gold	B=Black W=White U=Blue	A=Tray			



PCB LAYOUT

REVISION RECORD

REV	ECN	DESCRIPTION	DRFT	DATE
A0		NEW	R.Q	2021.12.15

DRAW		OPERATION		SCALE	FIT	JILN ® 东莞市锦凌电子有限公司 DONGGUAN JINLING ELECTRONIC CO.,LTD	
		X.X	±0.30	UNIT	mm		
CHECK		X.XX	±0.20	SIZE	A4	PART NO.	6235-03F15XXRXAXX
		X.XXX	±0.10	SHEET	1/1	TITLE:	HDR-15P母/铆锁带螺丝
APPROVE		Angle	±3°	PROJ.			