

G

F

F

Ordering Information

6235-02 M 25 XX S X A XX

Connector Type
F=Female
M=Male

No. of Pins
9,15,
25,37P

Contact
S0:Gold Flash/Tin
C0:Gold Flash
G2:2u" Gold
G3:3u" Gold
G4:5u" Gold

Plating

Color
B=Black
W=White
U=Blue

Packing
A=Tray

Serial code

B

A

1

2

3

4

5

6

7

3

C

REVISION RECORD

RFV

FCN

DESCRIPTION

DRAFT





DATE

AO	
----	--

NEW

	R.O
--	-----

2021.12.15



Recommended P. C. B Layout

Top View

Tolerance: $\pm 0.05\text{mm}$

DRAW		OPERATION		SCALE	FIT	 东莞市锦凌电子有限公司 DONGGUAN JINLING ELECTRONIC CO.,LTD	
		X.X	±0.30	UNIT	mm		
CHECK		X.XX	±0.20	SIZE	A4	PART NO.	6235-02M25XXSXAXX
		X.XXX	±0.10	SHEET	1/1		
APPROVE		Angle	±3°	PROJ.		TITLE:	DP-25P公/鲫鱼叉锁螺丝