



PCB.WELDING DRAWING (TOLERANCE:±0.05)



Main technical performance

Rated electrical load	DC 30V 5A
Contact resistance	≤30mΩ
Insulation resistance	≥100MΩ
Pressure resistance	AC 500V 1min
Insertion force	3-25N
Operating temperature range	-20C°~+70C°
service life	5000cycles

6	插片	1	黄铜	0.25T	雾锡金
5	内接触脚	1	磷铜	0.2T	雾锡金
4	外接触脚	1	磷铜	0.2T	雾锡金
3	外壳	1	磷铜	0.25T	镀银
2	盖片	1	PPA		
1	基座	1	PPA		
序号	产品名称	QIY	材料	规格	电镀

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdUNLESS OTHERWISE
SPECIFIED TOLERANCESTITLE:
DC SOCKET

PAR DC-517W-ARD100

DWN

CHKD

APVD

SCALE N:A UNIT:MM

SIZE:A4 SHEET:1F1



REV:A

DECIMALS:

X.X±0.30

X.XX±0.25

X.XXX±0.15

ANGLES:

X.*±5°

X.X°±1°

CUSTOMER COPY