













PCB.WELDING DRAWING (TOLERANCE:±0.05)

Main technical performance	
Rated electrical load	DC 20V 6.5A
Contact resistance	≤30mΩ
Insulation resistance	≥100MΩ
Pressure resistance	AC 500V 1min
Insertion force	3-20N
Operating temperature range	-20C°~+70C°
service life	5000cycles



SCHEMATIC



D	SHELL	1	COPPER ALLOY	Ni 50u"MIN.
C	SPRING	1	COPPER ALLOY	GOLD FLASH/MATTE TIN 80u"/Ni 40u"
B	CENTER PIN	1	COPPER ALLOY	GOLD FLASH/MATTE TIN 80u"/Ni 40u"
A	HOUSING	1	HIGH TEMP.THERMOPLASTIC	BLACK
NO.	DESCRIPTION	QTY	MATERIAL	REMARKS
MANUFACTURE DWG			 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			 TITLE: DC SOCKET	
DECIMALS:		ANGLES:	PAR	DC-516-ARF075
X.X±0.30		X.*±5°	DWN	
X.XX±0.25		X.X°±1°	CHKD	
X.XXX±0.15			APVD	
CUSTOMER COPY			SCALE N:A	UNIT:MM
			SIZE:A4	SHEET:1F1
				REV:A