

G
F
E
D
C
B
A

1. Rated voltage : 250V(Max)
2. Current Rating: 3.0 AMP (Max.)
3. Contact Resistance: 30mΩ (Max.)
4. Withstanding voltage : 1000V AC/Minute
5. Insulation Resistance: 1000MΩ (Min)
6. Operation Temperature: -40℃ to +105℃

- 1.Housing : PBT (UL94V-0)
- 2.Contact : Copper Alloy, Au/Sn over Ni Plating
- 3.Shell : Steel, Ni Plated
- 4.Screw : SWRCH, Ni Plated
- 5.Harpoon : Copper Alloy, Tin Plated

6235-02 M 15 XX S X A XX

Connector Type
F=Female
M=Male

No. of Pins
9,15,
25,37P


Contact
S0:Gold
G0:Gold
G2:2u" Gold
G3:3u" Gold
G4:5u" Gold

Plating
Flash/Tin
Flash

Color
B=Black
W=White
U=Blue

Packing
A=Tray

Serial code



1	2	3	4	5	6	7	8	9
---	---	---	---	---	---	---	---	---