

RoHS

NOTES:


- 1.Rated voltage : 250V(Max)
- 2.Current Rating: 3.0 AMP (Max.)
- 3.Contact Resistance: 30mΩ (Max.)
- 4.Withstanding voltage : 1000V AC/Minute
- 5.Insulation Resistance: 1000MΩ (Min)
- 6.Operation Temperature: -40℃ to +105℃

MATERIAL:

- 1.Housing : PBT (UL94V-0)
- 2.Contact : Copper Alloy, Au/Sn over Ni Plating
- 3.Shell : Steel, Ni or Sn Plated



REVISION RECORD

REV	ECN	DESCRIPTION	DRFT	DATE
A0		NEW	R.Q	2021.12.15



Ordering Information

6235-02	M	09	XX	D	X	A	XX
Connector Type	No.of Pins	Contact	Plating		Color	Packing	Serial code
F=Female M=Male	09,15, 25,37P	S0:Gold G0:Gold G2:2u" Gold G3:3u" Gold G4:5u" Gold	Flash/Tin Flash		B=Black W=White U=Blue	A=Tray	



DRAW		OPERATION		SCALE	FIT	JILN ® 东莞市锦凌电子有限公司 DONGGUAN JINLING ELECTRONIC CO.,LTD	
		X.X	±0.30	UNIT	mm		
CHECK		X.XX	±0.20	SIZE	A4	PART NO.	6235-02M09XXDXAXX
		X.XXX	±0.10	SHEET	1/1	TITLE:	DB-9P公/传统焊线式
APPROVE		Angle	±3°	PROJ.			