





SPECIFICATIONS

Current Rating: 1.0 Amps
Withstanding Voltage: AC 500V
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Operation Temperature: -40° to +105°
Insulator Material: Polyester (UL94V-0)
Contact Material: Phosphor bronze
Standard: PA6T
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

Part No	Pin	A	B	Part No	Pin	A	B	Part No	Pin	A	B	Part No	Pin	A	B
PM1.27-UP1S-1A	1	-	-	PM1.27-UP1S-11A	11	12.70	13.97	PM1.27-UP1S-21A	21	25.40	26.67	PM1.27-UP1S-31A	31	38.10	39.37
PM1.27-UP1S-2A	2	1.27	2.54	PM1.27-UP1S-12A	12	13.97	15.24	PM1.27-UP1S-22A	22	26.67	27.94	PM1.27-UP1S-32A	32	39.37	40.64
PM1.27-UP1S-3A	3	2.54	3.81	PM1.27-UP1S-13A	13	15.24	16.51	PM1.27-UP1S-23A	23	27.94	29.21	PM1.27-UP1S-33A	33	40.64	41.91
PM1.27-UP1S-4A	4	3.81	5.08	PM1.27-UP1S-14A	14	16.51	17.78	PM1.27-UP1S-24A	24	29.21	30.48	PM1.27-UP1S-34A	34	41.91	43.18
PM1.27-UP1S-5A	5	5.08	6.35	PM1.27-UP1S-15A	15	17.78	19.05	PM1.27-UP1S-25A	25	30.48	31.75	PM1.27-UP1S-35A	35	43.18	44.45
PM1.27-UP1S-6A	6	6.35	7.62	PM1.27-UP1S-16A	16	19.05	20.32	PM1.27-UP1S-26A	26	31.75	33.02	PM1.27-UP1S-36A	36	44.45	45.72
PM1.27-UP1S-7A	7	7.62	8.89	PM1.27-UP1S-17A	17	20.32	21.59	PM1.27-UP1S-27A	27	33.02	34.29	PM1.27-UP1S-37A	37	45.72	46.99
PM1.27-UP1S-8A	8	8.89	10.16	PM1.27-UP1S-18A	18	21.59	22.86	PM1.27-UP1S-28A	28	34.29	35.56	PM1.27-UP1S-38A	38	46.99	48.26
PM1.27-UP1S-9A	9	10.16	11.43	PM1.27-UP1S-19A	19	22.86	24.13	PM1.27-UP1S-29A	29	35.56	36.83	PM1.27-UP1S-39A	39	48.26	49.53
PM1.27-UP1S-10A	10	11.43	12.70	PM1.27-UP1S-20A	20	24.13	25.40	PM1.27-UP1S-30A	30	36.83	38.10	PM1.27-UP1S-40A	40	49.53	50.80

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.35	X.*± 5°	APR. Alex	TITLE: 1.27PM H4.3 2xnPin 180° W3.0 U型 PC2.4 6T		
.XX±0.25	.X.*± 3°	CHK. Jack	DWG NO. PM1.27-UP1S-NA		
.XXX±0.15	.XX.*± 1°	DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1/1