













PCB.WELDING DRAWING (TOLERANCE:±0.05)

Main technical performance

Rated electrical load	DC 20V 5A
Contact resistance	≤30mΩ
Insulation resistance	≥100MΩ
Pressure resistance	AC 500V 1min
Insertion force	3-25N
Operating temperature range	-20℃~+70℃
service life	5000cycles

SCHEMATIC



4	圆针	1	黄铜	镀银
3	插片	1	黄铜	镀银
2	弹片	1	磷铜	镀银
1	基座	1	PPA(黑色)	
序号	名称	数量	材料	备注
MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: DC SOCKET		
DECIMALS:		PAR		DC-515-ACL075
ANGLES:		DWN		
X.X±0.30		CHKD		
X.XX±0.25		APVD		
X.XXX±0.15		SCALE N:A		UNIT:MM
		CUSTOMER COPY		SIZE:A4
				SHEET:1F1
				REV:A