







PCB.WELDING DRAWING (TOLERANCE:±0.05)



Main technical performance	
Rated electrical load	DC 30V 5A
Contact resistance	$\leq 30m\Omega$
Insulation resistance	$\geq 100M\Omega$
Pressure resistance	AC 500V 1min
Insertion force	3-25N
Operating temperature range	-20℃~+70℃
service life	5000cycles

6	插片	1	黄铜	0.25T	雾锡金
5	内接触脚	1	磷铜	0.2T	雾锡金
4	外接触脚	1	磷铜	0.2T	雾锡金
3	外壳	1	磷铜	0.25T	镀银
2	盖片	1	PPA		
1	基座	1	PPA		
序号	产品名称	QIY	材料	规格	电镀

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdUNLESS OTHERWISE
SPECIFIED TOLERANCESTITLE:
DC SOCKET

DECIMALS:	ANGLES:
X.X±0.30	X.*±5°
X.XX±0.25	X.X°±1°
X.XXX±0.15	

CUSTOMER COPY

PAR	DC-517D--ARD100
DWN	
CHKD	
APVD	
SCALE N:A	UNIT:MM
SIZE:A4	SHEET:1F1
	REV:A