




备注(NOTE): 1 材质:

1.1 胶芯: LCP UL94 V-0

1.2 端子: (C2680;; 镍底, 镀金0.5U

1.3 外壳: 不锈钢304—表面镀镍50U

2. 电气特性:

2.1. 接触区: 接触电阻30mQMax, 允许10mΩ变化量, 测试条件: 20mv,100mA下测量,

2.2. 额定电流: 最大3A

2.3. 额定电压: 5V.

2.4. 耐电压: 100VAC.

2.5. 绝缘电阻: 至少100兆欧

3. 机械性能:

3.1. 插入力: 0.5—2.0Kg

3.2. 拔出力: 0.8—2.0Kg

3.3. 插拔次数: 5000+.

4. 工作环境: -20℃to +85℃

4.1. 盐雾测试: 24H

USB TYPE-C PIN ASSIGNMENTS	
PIN NUMBER	PIN NUMBER
A5	CC1
A9	VBUS
A12	GND
B12	GND
B9	VBUS
B5	CC2

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					
DIM. TOL.		TITLE: USB-type C 6pin 6.5 母座直立式贴板成品					
X ±0.30		DWG. NO.: UC16-0B06F65011		DRAWN: MAX			
X.X ±0.25		PART NO.: UC16-0B06F65011		CHECKED: ELLA			
X.XX ±0.15		UNIT: mm		APPROVED: WILL			
X.XXX ±0.15		SCALE: none		SHEET: 1 of 1			
GENERAL ANGLE: ±3°		DWG. SIZE: A4		LAYER: bxconn			