




WWW.BXCONN.COM 东莞市宝讯精密技术有限公司 ARTICLE: BX-CN-001-A


A		B		C		D		E	
				REV.	DESCRIPTION		ECN NO.	NAME	DATE



RECOMMENDED PCB LAYOUT(TOP VIEW)
THICKNESS SEE TABLE1;DEFAULT TOLERANCE:±0.05

TABLE 1

P/N	DIM A	DIM B	DIM C	DIM D	THICKNESS OF THE PCB	QTY/TUBE	QTY/BOX
TYPEC-1103-BRP24	10.40	0.45	0.80	0.82	0.80±0.05MM	50	18000

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD						
DIM. X X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 GENERAL ANGLE: ±3° 	TOL.		TITLE: USB C F SPLINT CONN. WITH EMI PCB=0.8&1.0					
	DWG. NO.: UC13-0B24F00P11			DRAWN: MAX				
	PART NO.: UC13-0B24F00P11			CHECKED: ELLA				
	UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL		