

规格书 SPECIFICATION

型 号 Model		RF0.81双银		截面图Section		
规 格 Size		/				
标 准 号Standard		/				
导体 Conductor	结构Construction D/mm	7/0.05SPC				
	单支直径Single Diameter ±0.008mm	0.05±0.008				
	直径Diameter mm	0.15				
	绞距Lay Length mm	≤2.5				
绝缘体 Insulator	厚度Thickness mm	0.31		印字Marking	NO MARKING	
	外径Diameter mm	0.41±0.02				
	颜色Color	透明				
	材质 Material	FEP				
屏蔽层 Shielding Layer	单支直径Single Diameter ±0.005mm	0.05SPC				
	锭数*支数 锭*根 屏蔽率	16/3/0.05 90%以上				
护套 Jacket	厚度Thickness mm	0.10		衰减 ATTENUATION (dB/M)		
	外径Diameter mm	0.81±0.05				
	颜色Color	所有颜色				
	材质 Material	FEP				
性能 Function	额定温度, 电压 Rated Temperature Voltage °C V	-55~200°C 30V		1GHz 3.10		
	电容 Capacitance(pF/m)	98		2GHz 4.70		
	速率 Velocity(100%)	70		3GHz 5.80		
	驻波比 VSWR	≤1.30@DC-6GHZ		4GHz 6.90		
客户意见 Customer suggest		产品编号 Product Code	版本 Edition	客户代码 Customer Code	日期 Date	
		RF0.81双银	A/1			
客户核准 Customer confirm		核准Checked BY	制作Designed BY			
		屈代军2024/7/30				