






[illegible][illegible][illegible][illegible]

A

B

C

D

E

REV.

DESCRIPTION

ECN NO.

NAME

DATE

1

2

PLUG

6.65

2.05

AFTER MATING

USB TYPE-C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND

6.40

4.80

3.50

2.50

1.50

0.50

0.30(8X)

0.60(4X)

1.90(2X)

1.50(2X)

1.10(2X)

1.50(2X)

0.60(4X)

1.00(4X)

9.24

11.24

4.00

4.60

5.70

P.C.B EDGE

PRODUCT EDGE

RECOMMENDED PCB LAYOUT(TOP VIEW)
THICKNESS 0.80MM;DEFAULT TOLERANCE:±0.05

GENERAL TOLERANCE

DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD

DIM.

X
X.X
X.XX
X.XXX

TOL.

±0.30
±0.25
±0.15

GENERAL ANGLE:

±3°

TITLE: USB CF 16PIN (L=6.5) MID MOUNT 0.8MM

DWG. NO.: UC01-OB16F08011DRAWN: MAX

PART NO.: UC01-OB16F08011CHECKED: ELLA

UNIT:mmSCALE:noneSHEET:1of 1DWG. SIZE:A4LAYER:bxconnAPPROVED: WILL

BXCONN®