

规格书 SPECIFICATION

型 号 Model		RF1.37单银		截面图Section		
规 格 Size		/				
标 准 号Standard		/				
导体 Conductor	结构Construction D/mm	7/0.10SPC				
	单支直径Single Diameter ±0.008mm	0.1±0.008				
	直径Diameter mm	0.3				
	绞距Lay Length mm	≤4.5				
绝缘体 Insulator	厚度Thickness mm	0.30		印字Marking	NO MARKING	
	外径Diameter mm	0.90±0.03				
	颜色Color	透明				
	材质 Material	FEP				
屏蔽层 Shielding Layer	单支直径Single Diameter ±0.005mm	0.05TD				
	锭数*支数 锭*根 屏蔽率	16/5/0.05 85%以上				
护套 Jacket	厚度Thickness mm	0.12		衰减 ATTENUATION (dB/M)		
	外径Diameter mm	1.37±0.05				
	颜色Color	所有颜色				
	材质 Material	FEP				
性能 Function	额定温度, 电压 Rated Temperature Voltage °C V	-55~200°C 30V		1GHz 1.70		
	电容 Capacitance(pF/m)	96		2GHz 2.50		
	速率 Velocity(100%)	70		3GHz 3.00		
	驻波比 VSWR	≤1.30@DC-6GHZ		4GHz 3.50		
客户意见 Customer suggest		产品编号 Product Code		版本 Edition	客户代码 Customer Code	日期 Date
		RF1.37单银		A/1		
		客户核准 Customer confirm		核准Checked BY		制作Designed BY
				屈代军2024/7/30		