



A	B	C	D	E
---	---	---	---	---

REV.	DESCRIPTION	ECN NO.	NAME	DATE

1



2



备注(NOTE): 1 材质:

1.1 胶芯: LCP UL94 V-0

1.2 端子: (C2680), 镍底, 镀金 0.5U

1.3 外壳: 不锈钢304—表面镀镍50U

2. 电气特性:

2.1. 接触区: 接触电阻30mQMax, 允许10mΩ变化量,

测试条件: 20mv,100mA下测量,

2.2. 接触电流: 3AVBUS引脚: 1.25A

用于GND引脚: 其他引脚为0.25A.

2.3. 额定电压: 5V.

2.4. 耐电电压: 100VAC.

2.5. 绝缘电阻: 至少100兆欧

3. 机械性能:

3.1. 插入力: 0.5—2.0Kg




3.2. 拔出力: 0.6—2.0Kg

3.3. 插拔次数: 5000+.




4. 工作环境: -20℃to +85℃

4.1. 盐雾测试: 24H

3





4



5

PIN ASSIGNMENTS

A5	CC1	B12	GND
A9	VBUS	B9	VBUS
A12	GND	B5	CC2
PIN	SIGNAL NAME	PIN	SIGNAL NAME

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				 		
DIM.	TOL.	TITLE: USB-type C 6pin母座 L=6.0mm成品						
X		DWG. NO.: UC21-OB06F60011		DRAWN: MAX				
X.X	±0.30	PART NO.: UC21-OB06F60011						
X.XX	±0.25						CHECKED: ELLA	
X.XXX	±0.15	UNIT: mm		SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL
GENERAL ANGLE: ±3°								