




1		2		3		4		5		6		7		8		9																
G		RoHS																G														
F		SPECIFICATIONS														F																
E		Rated Current:3.0AMP Contact Resistance:20mΩ Max Withstand Voltage:1000V AC/DC Insulation Resistance:1000MΩ Min Operation Temperature:-40°c to +105°c														E																
D		Contact Material:Brass Contact Plating:Au Over Ni Insulator Material:Polyester(UL94V-0) Standard: PA6T Max.Processing Temp: 230°C for 30-60 seconds (260°C for 10 seconds)														D																
C																C																
B						<table border="1"><caption>Dimension antitheses list</caption><thead><tr><th>ITEM</th><th>PA</th><th>PB</th><th>PC</th><th>L</th></tr></thead><tbody><tr><td>Standard</td><td>6.00</td><td>4.30</td><td>3.00</td><td>13.80</td></tr><tr><td>Alternate</td><td></td><td></td><td></td><td></td></tr></tbody></table>										ITEM	PA	PB	PC	L	Standard	6.00	4.30	3.00	13.80	Alternate					B	
ITEM	PA	PB	PC	L																												
Standard	6.00	4.30	3.00	13.80																												
Alternate																																
A						OPERATION		DRAW				SCALE		FIT		深圳市连盛精密连接器有限公司																
						X.X ±0.30						UNIT		mm																		
						X.XX ±0.20		CHECK				SIZE		A4																		
A0		2012.07.02		NEW DRAWING		X.XXX ±0.10						SHEET		1/1																		
REV		DATE		MODIFICATION DESCRIPTION		CHANGE		DIM		TOL		PROJ.				TITLE:																
1		2		3		4		5		6		7		8		9																



Dimension antitheses list				
ITEM	PA	PB	PC	L
Standard	6.00	4.30	3.00	13.80
Alternate				

				OPERATION		DRAW			SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30				UNIT	mm		
				X.XX	±0.20	CHECK			SIZE	A4	PART NO.	
A0	2012.07.02	NEW DRAWING		X.XXX	±0.10				SHEET	1/1		
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	Angle	±3°	APPROVE			PROJ.		TITLE:	2.54PH 2.5mm 1X40 90°正弯
				DIM	TOL							