




A向旋转



Circuit Diagram



PCBLayout(Top view)

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑥	Contact	1	SUS			
⑤	Cover	1	PA66	White		
④	LED	1	GaASP/GaP			
③	Terminal	8	Brass	Ag Plating		
②	Base	1	PA66	Black		
①	Button	1	PA66	White		



APPROVALS		DATE
DRAWN	LIUCAN	2021.09.30

TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
	10~30	±0.20				
	5~10	±0.15	±2°			
	~ 5	±0.10				

## Typical Specifications

- Rating : DC 30V 30mA
- Insulation Resistance : 100mΩ Min
- Dielectric Strength : AC 250V for 1 minute
- Operating Force : 260±50 gf
- Contact Resistance : 50mΩ MAX
- Life : 100,000 Cycles Min

—	A	—	NEW	—	—	
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.